
## Bonding/Grounding Straps

Harger's Complete Line of Bonding/Grounding Straps are Unparalleled!

- High quality straps for today's demanding power and grounding applications.
- Offer flexible bonding between bond points such as switchgear, substation, transformer and generators.

Providing a superior/low resistance permanant ground path, Harger's line of Bonding/Grounding Straps deliver the power and reliability your next bonding and grounding project needs.




Part No.	Amps	Number of Braids	"W" Terminal Width	"L" Terminal End to End	Hole O.C. Spacing	Hardware Size	Qty.	Approx. Each Wt. (lbs.)
BGS37C12D2D	470	3	1"	12"	1-3/4"	1/2"	EA	1
BGS37C12E2C	470	3	1"	12"	1-1/4"	3/8"	EA	1
BGS39A12D2D	190	1	1"	12"	1-3/4"	1/2"	EA	1
BGS39A12E2C	190	1	1"	12"	1-1/4"	3/8"	EA	1
BGS39A18D2D	190	1	1"	18"	1-3/4"	1/2"	EA	1
BGS39A18E2C	190	1	1"	18"	1-1/4"	3/8"	EA	1
BGS39A24D2D	190	1	1"	24"	1-3/4"	1/2"	EA	1
BGS39A24E2C	190	1	1"	24"	1-1/4"	3/8"	EA	1
BGS39B12D2D	360	2	1"	12"	1-3/4"	1/2"	EA	1
BGS39B12E2C	360	2	1"	12"	1-1/4"	3/8"	EA	1
BGS39B12F2C	360	2	1"	12"	1-1/2"	3/8"	EA	1
BGS39B18D2D	360	2	1"	18"	1-3/4"	1/2"	EA	2
BGS39B18F2C	360	2	1"	18"	1-1/2"	3/8"	EA	2
BGS39B24D2D	360	2	1"	24"	1-3/4"	1/2"	EA	2
BGS39B24F2C	360	2	1"	24"	1-1/2"	3/8"	EA	2
BGS39D12D2D	600	4	1"	12"	1-3/4"	1/2"	EA	2
BGS39D12E2C	600	4	1"	12"	1-1/4"	3/8"	EA	2
BGS49C12D2D	515	3	1.375"	12"	1-3/4"	1/2"	EA	2
BGS49C12F2C	515	3	1.375"	12"	1-1/2"	3/8"	EA	2
BGS51B12D2D	530	2	2"	12"	1-3/4"	1/2"	EA	2
BGS51B12F2C	530	2	2"	12"	1-1/2"	3/8"	EA	2
BGS51C12D2D	600	3	2"	12"	1-3/4"	1/2"	EA	2
BGS51C12F2C	600	3	2"	12"	1-1/2"	3/8"	EA	2

More part numbers on back page.







- Terminal ends come tinned as standard
- Bare, silver, nickel are available
- Ends swedged to braid

- **Braid**
- Pure copper braid Electro-tin plated as standard
- Flexible braid for bonding misaligned bond points
- RoHS Compliant

Part No.	Amps	Number of Braids	"W" Terminal Width	"L" Terminal End to End	Hole O.C. Spacing	Hardware Size	Qty.	Approx. Each Wt. (lbs.)
BGS52B12D2D	530	2	2"	12"	1-3/4"	1/2"	EA	2
BGS52B12F2C	530	2	2"	12"	1-1/2"	3/8"	EA	2
BGS52B18D2D	530	2	2"	18"	1-3/4"	1/2"	EA	3
BGS52B18F2C	530	2	2"	18"	1-1/2"	3/8"	EA	3
BGS52B24D2D	530	2	2"	24"	1-3/4"	1/2"	EA	3
BGS52B24F2C	530	2	2"	24"	1-1/2"	3/8"	EA	3
BGS52D12D2D	530	4	2"	12"	1-3/4"	1/2"	EA	3
BGS52D12F2C	530	4	2"	12"	1-1/2"	3/8"	EA	3
BGS53B12D2D	520	2	2"	12"	1-3/4"	1/2"	EA	2
BGS53C12D2D	700	3	2"	12"	1-3/4"	1/2"	EA	3
BGS53C12F2C	700	3	2"	12"	1-1/2"	3/8"	EA	3
BGS53D12D2D	800	4	2"	12"	1-3/4"	1/2"	EA	3
BGS53D12F2C	800	4	2"	12"	1-1/2"	3/8"	EA	3
BGS56D12D2D	1000	4	2-1/2"	12"	1-3/4"	1/2"	EA	5
BGS61A12D2D	415	1	1-1/2"	12"	1-3/4"	1/2"	EA	2
BGS61A12F2C	415	1	1-1/2"	12"	1-1/2"	3/8"	EA	2
BGS61A18D2D	415	1	1-1/2"	18"	1-3/4"	1/2"	EA	3
BGS61A18F2C	415	1	1-1/2"	18"	1-1/2"	3/8"	EA	3
BGS61A24D2D	415	1	1-1/2"	24"	1-3/4"	1/2"	EA	3
BGS61A24F2C	415	1	1-1/2"	24"	1-1/2"	3/8"	EA	3

Other sizes are available. Please contact factory for more information.



301 Ziegler Drive, Grayslake, IL, 60030 p: 800.842.7437 • 847.548.8700

website: www.harger.com • email: hargersales@harger.com