



**#R4150-A4
INSULATOR**

Voltage Rating - 2,000 volts

Dimension A is 1-3/4"

Dimension B is 1-7/8"

Physical Properties	Electrical Properties
Tensile Strength (lbs.)	2500-2700
Cantilever Strength (in. lbs.)	2500-3750
Compression Strength (lbs.)	17000
Thread Stripping Torque (ft. lbs.)	30
Dielectric Strength (volts S.T.)	15000
Arc Resistance (sec. ASTM D495)	180+
Flame Retardance (sec. ign./sec. burn, Fed. Std. 2023)	UL 94-V0
Water Absorption (% in 24 hrs. @ 23°C)	0.15
Height Tolerance (in.)	± .015
Creep Distance (in.)	1/4" + Ht.