



#BGC4SCS Conduit Bonding Clamp

DESCRIPTION

- “Low Profile” design utilizes 1/4” diameter x 1/2” long hex head cap screws instead of 1/4” diameter x 1-1/2” long slotted head machine screws.
- Accepts conductors from #10 AWG through #2 AWG.
- Fits 1/2” to 1” conduits.
- Hex head cap screw fits 7/16” nut driver, socket or wrench.

APPLICATION

- For bonding conduits that are flush mounted to a surface such as a wall, floor or ceiling.