



213TTP Cable to Flat Metal Connector with Tamper Resistant Hardware

DESCRIPTION

- 1-3/4" x 2" two piece, one bolt tamper resistant connector
- Accommodates conductors from #6 AWG to 250MCM or 0.575" diameter to flat metal objects up to .5" thickness
- Manufactured from high conductivity electro tin plated bronze
- Breakaway nut fractures at a torque rating of 120 inch/lbs
- UL 96 and 467 listed

APPLICATIONS

- Used in high theft areas when bonding to I-Beams and channel up to 1/2" thick
- Suitable for direct burial