



219-3/8 Bolt Hole Bonding Plate

Description

- Copper bolt hole bonding plate with 3/8" tapped hole
- 2-1/2" x 4" cast bonding plate provides over 8 square inches of bonding surface
- Dual pressure type cable connector will accept all main size conductors up to 9/16" in diameter

Application

- Used over anchor bolts to ground steel columns
- Recommended installation tool - 1/2" socket wrench, end wrench, or nut driver

Box Qty.	Approx. Box Wt. (lbs.)
5	3.75