



223T
Tin Plated Flange Bonding Plate

DESCRIPTION

- 4" x 3-3/4" bonding plate provides over 8 square inches of bonding surface
- Manufactured from high conductivity copper alloy
- Large cable connector offers 3" of contact between the bonding plate and the cable
- Accommodates bonding and grounding conductors from #6 AWG stranded (#4 AWG solid) to 500MCM stranded and solid or 0.813" diameter and all main sized lightning and lightning bonding conductors
- Electro-tin plated for material compatibility and corrosion resistance.
- UL 96 and 467 listed

APPLICATIONS

- Used when bonding to I-Beams up to 1" thick
- · Suitable for direct burial