



223TTP Flange Bonding Plate with Tamper Resistant Hardware

DESCRIPTION

- 4" x 3-3/4" bonding plate provides over 8 square inches of bonding surface
- Manufactured from electro tin-plated bronze
- Cable connector provides 3" of contact between the bonding plate and the cable
- Accommodates conductors from #6 AWG to 500MCM or 0.813" diameter
- Breakaway nut fractures at a torque rating of 120 inch/lbs
- UL 96 and 467 listed

APPLICATIONS

- Used in high theft areas when bonding to I-Beams up to 1" thick
- Suitable for direct burial