

#CPC Series PIPE GROUNDING CONNECTORS

DESCRIPTION

- Manufactured from electroplated tinned bronze
- Wider conductor range; #6 up to 250 MCM
- Features “quick connect”, bi-directional design
- Dual UL listing; exceeds direct burial requirements

Product Number	Nominal Pipe Size Range	Outside Diameter Pipe Size Range	Approx. Unit Wt. (lbs.)	Approx. Box Wt. (lbs.)	Box Qty.
CPC .5/.75	.5" - .75"	.375" – 1"	1/2	2-1/2	5
CPC 1/1.25	1" – 1.25"	.75" – 1.7"	1/2	3	5
CPC 1.5/2	1.5" – 2"	1" – 2.4"	1/2	3-3/4	5
CPC 2.5/3	2.5" – 3"	2.25" – 3.5"	3/4	5	5
CPC 3.5/4	3.5" – 4"	3.2" – 4.5"	1-1/4	6-1/4	5
CPC 5/6	5" – 6"	5.63" – 6.63"	1-3/4	8-3/4	5

