



FBS1/0RB
1/0 AWG Ropelay
Flexible Butt End Splice of Horizontal Cables

DESCRIPTION

- Flexible butt end splice of 1/0 AWG Ropelay cables, horizontal
- 0.42” recommended bare conductor O.D.
- 0.55” finished weld O.D.
- Requires the use of high temperature glass cloth electrical tape
- Uses US90 or NUWTUBE90
- Use with mold handle MH1