



**FBS2/0RB**  
**2/0 AWG Ropelay**  
**Flexible Butt End Splice of Horizontal Cables**

DESCRIPTION

- Flexible butt end splice of 2/0 AWG Ropelay cables, horizontal
- 0.46” recommended bare conductor O.D.
- 0.57” finished weld O.D.
- Requires the use of high temperature glass cloth electrical tape
- Uses US90 or NUWTUBE90
- Use with mold handle MH1