



FBS2RB
#2 AWG Ropelay
Flexible Butt End Splice of Horizontal Cables

DESCRIPTION

- Flexible butt end splice of #2 AWG Ropelay cables, horizontal
- 0.33" recommended bare conductor O.D.
- 0.46" finished weld O.D.
- Requires the use of high temperature glass cloth electrical tape
- Uses US65 or NUWTUBE65
- Use with mold handle MH1