



**FBS4/0RB**  
**4/0 AWG Ropelay**  
**Flexible Butt End Splice of Horizontal Cables**

DESCRIPTION

- Flexible butt end splice of 4/0 AWG Ropelay cables, horizontal
- 0.59" recommended bare conductor O.D.
- 0.73" finished weld O.D.
- Requires the use of high temperature glass cloth electrical tape
- Uses US115 or NUWTUBE115
- Use with mold handle MH1