



**FBS4RB**  
**#4 AWG Ropelay**  
**Flexible Butt End Splice of Horizontal Cables**

DESCRIPTION

- Flexible butt end splice of #4 AWG Ropelay cables, horizontal
- 0.26" recommended bare conductor O.D.
- 0.40" finished weld O.D.
- Requires the use of high temperature glass cloth electrical tape
- Uses US45 or NUWTUBE45
- Use with mold handle MH1