



FBS8RL
#8 AWG Ropelay
Flexible Butt End Splice of Horizontal Cables

DESCRIPTION

- Flexible butt end splice of #8 AWG Ropelay cables, horizontal
- 0.16” recommended bare conductor O.D.
- 0.31” finished weld O.D.
- Requires the use of high temperature glass cloth electrical tape
- Uses US25 or NUWTUBE25
- Mold handle included