



TBC22 Tower Bonding Clamp

Description

- Copper flange bonding plate
- Simple two bolt installation
- Wide flange range (0.125" - 0.625")

Application

- Large cable connector offers grounding point for towers and structure steel
- Ships with #2 AWG two hole compression lug
- UL 467 Listed

Box Qty.	Approx. Box Wt. (lbs.)
10	10

03/05/2023