



Cable to Cable Connections



(Parallel Thru Splice of Horizontal Cables, Tap Conductor Over Run)

PT Connection Type

Cable Size		Mold Part No.	Weld Metal	
Run	Tap		UltraShot	NUWTUBE
#2 Sol	#2 Sol	PT-2S2SB	US65	NUWTUBE65
#2	#6	PT-26B	US45	NUWTUBE45
	#4	PT-24B	US65	NUWTUBE65
	#2	PT-22B	US65	NUWTUBE65
1/0	#2	PT-1/02B	US65	NUWTUBE65
	1/0	PT-1/01/0B	US90	NUWTUBE90
2/0	#2	PT-2/02B	US90	NUWTUBE90
	1/0	PT-2/01/0B	US115	NUWTUBE115
	2/0	PT-2/02/0B	US115	NUWTUBE115
4/0	#4	PT-4/04B	US150	NUWTUBE150
	#2	PT-4/02B	US150	NUWTUBE150
	1/0	PT-4/01/0B	US150	NUWTUBE150
	2/0	PT-4/02/0B	US150	NUWTUBE150
	3/0	PT-4/03/0B	US200	NUWTUBE200
	4/0	PT-4/04/0B	US200	NUWTUBE200




(Cross of Horizontal Cables, Lapped & Not Cut)

XO Connection Type

Cable Size		Mold Part No.	Weld Metal	
Run	Tap		UltraShot	NUWTUBE
2/0	#2	XO-2/02Q	US150	NUWTUBE150
	1/0	XO-2/01/0Q	US200	NUWTUBE200
	2/0	XO-2/02/0Q	US200	NUWTUBE200
4/0	#2	XO-4/02Q	US150	NUWTUBE150
	1/0	XO-4/01/0Q	US200	NUWTUBE200
	2/0	XO-4/02/0Q	US200	NUWTUBE200
	3/0	XO-4/03/0Q	US250	NUWTUBE250
	4/0	XO-4/04/0I*	US250	NUWTUBE250
250 MCM	250 MCM	XO-25CM25CM*	US300	2-NUWTUBE150


*New innovative 3 piece design.



(Tee of Horizontal Run & Tap Cables)

RT Connection Type

Cable Size		Mold Part No.	Weld Metal	
Run	Tap		UltraShot	NUWTUBE
#2 Sol	#2 Sol	RT-2S2SB	US45	NUWTUBE45
#2	#2	RT-22B	US45	NUWTUBE45
1/0	#2	RT-1/02B	US45	NUWTUBE45
	1/0	RT-1/01/0B	US90	NUWTUBE90
2/0	#2	RT-2/02B	US45	NUWTUBE45
	1/0	RT-2/01/0B	US90	NUWTUBE90
	2/0	RT-2/02/0B	US90	NUWTUBE90
3/0	#2	RT-3/02B	US45	NUWTUBE45
	1/0	RT-3/01/0B	US90	NUWTUBE90
	2/0	RT-3/02/0B	US90	NUWTUBE90
	3/0	RT-3/03/0B	US115	NUWTUBE115
4/0	#2	RT-4/02B	US90	NUWTUBE90
	1/0	RT-4/01/0B	US90	NUWTUBE90
	2/0	RT-4/02/0B	US90	NUWTUBE90
	3/0	RT-4/03/0B	US115	NUWTUBE115
	4/0	RT-4/04/0B	US150	NUWTUBE150



(Butt End Splice of Horizontal Cables)

BS Connection Type


Cable Size	Mold Part No.	Weld Metal	
		UltraShot	NUWTUBE
#6 Sol	BS-6SL	US25	NUWTUBE25
#4	BS-4L	US25	NUWTUBE25
#2	BS-2L	US32	NUWTUBE32
1/0	BS-1/0B	US45	NUWTUBE45
2/0	BS-2/0B	US65	NUWTUBE65
3/0	BS-3/0B	US90	NUWTUBE90
4/0	BS-4/0B	US90	NUWTUBE90
250 MCM	BS-25CMB	US115	NUWTUBE115

Handle Clamps Required:

MH1 for **B, K, P & Q** Price Key Molds
 MH2 for **C** Price Key Molds
 MH3 for GS Style **R** Price Key Molds
 MH6 for **I** Price Key Molds

L & M Price Key Molds INCLUDE MH3 Handle
A Price Key Molds SOLD WITH FRAME

Cable to Cable Connections



cUL US Listed 467
(Parallel Tap of
Horizontal Cables)

PB Connection Type

Cable Size		Mold Part No.	Weld Metal	
Run	Tap		UltraShot	NUWTUBE
#2 Sol	#2 Sol	PB-2S2SB	US65	NUWTUBE65
#2	#6	PB-26B	US32	NUWTUBE32
	#4	PB-24B	US45	NUWTUBE45
	#2	PB-22B	US65	NUWTUBE65
1/0	#6	PB-1/06B	US45	NUWTUBE45
	#4	PB-1/04B	US65	NUWTUBE65
	#2	PB-1/02B	US65	NUWTUBE65
	1/0	PB-1/01/0B	US90	NUWTUBE90
2/0	#6	PB-2/06B	US65	NUWTUBE65
	#4	PB-2/04B	US65	NUWTUBE65
	#2	PB-2/02B	US90	NUWTUBE90
	1/0	PB-2/01/0B	US115	NUWTUBE115
	2/0	PB-2/02/0B	US115	NUWTUBE115
4/0	#6	PB-4/06B	US90	NUWTUBE90
	#4	PB-4/04B	US90	NUWTUBE90
	#2	PB-4/02B	US115	NUWTUBE115
	1/0	PB-4/01/0B	US115	NUWTUBE115
	2/0	PB-4/02/0B	US115	NUWTUBE115
	4/0	PB-4/04/0B	US150	NUWTUBE150




(Parallel Thru Splice of
Horizontal Cables)

PS Connection Type

Cable Size		Mold Part No.	Weld Metal	
Run	Tap		UltraShot	NUWTUBE
#8 Sol	#8 Sol	PS-8S8SL	US25	NUWTUBE25
#8	#8	PS-88L	US25	NUWTUBE25
#6 Sol	#6 Sol	PS-6S6SL	US25	NUWTUBE25
#6	#6	PS-66L	US25	NUWTUBE25
#4 Sol	#4 Sol	PS-4S4SM	US32	NUWTUBE32
#4	#4	PS-44M	US32	NUWTUBE32
#2 Sol	#2 Sol	PS-2S2SM	US45	NUWTUBE45

Cable to Ground Rod Connections




cUL US Listed 467
(Single Cable Dead Ended to
Top of Ground Rod)

GD Connection Type

Ground Rod Size*	Cable Size	Mold Part No.	Weld Metal	
			UltraShot	NUWTUBE
5/8"	#2 Sol	GD-582SB	US65	NUWTUBE65
	#2	GD-582B	US65	NUWTUBE65
	1/0	GD-581/0B	US90	NUWTUBE90
	2/0	GD-582/0B	US90	NUWTUBE90
	3/0	GD-583/0B	US90	NUWTUBE90
	4/0	GD-584/0B	US90	NUWTUBE90
3/4"	#2 Sol	GD-342SB	US90	NUWTUBE90
	#2	GD-342B	US90	NUWTUBE90
	1/0	GD-341/0B	US90	NUWTUBE90
	2/0	GD-342/0B	US90	NUWTUBE90
	3/0	GD-343/0B	US90	NUWTUBE90
	4/0	GD-344/0B	US90	NUWTUBE90

*Copper-Clad ground rod nominal dimensions.




cUL US Listed 467
(Horizontal Thru Cable to
Top of Ground Rod)

GO Connection Type

Ground Rod Size*	Cable Size	Mold Part No.	Weld Metal	
			UltraShot	NUWTUBE
5/8"	#2 Sol	GO-582SB	US90	NUWTUBE90
	#2	GO-582B	US90	NUWTUBE90
	1/0	GO-581/0B	US90	NUWTUBE90
	2/0	GO-582/0B	US115	NUWTUBE115
	3/0	GO-583/0B	US115	NUWTUBE115
	4/0	GO-584/0B	US115	NUWTUBE115
3/4"	#2 Sol	GO-342SB	US90	NUWTUBE90
	#2	GO-342B	US90	NUWTUBE90
	1/0	GO-341/0B	US115	NUWTUBE115
	2/0	GO-342/0B	US115	NUWTUBE115
	3/0	GO-343/0B	US115	NUWTUBE115
	4/0	GO-344/0B	US115	NUWTUBE115

*Copper-Clad ground rod nominal dimensions.

Cable to Ground Rod Connections



c  US Listed 467


(Horizontal Thru Cable to Side of Ground Rod)

GS Connection Type

Ground Rod Size*	Cable Size	Mold Part No.	Weld Metal	
			UltraShot	NUWTUBE
5/8"	#2 Sol	GS-582SR	US65	NUWTUBE65
	#2	GS-582R	US65	NUWTUBE65
	1/0	GS-581/0P	US115	NUWTUBE115
	2/0	GS-582/0P	US115	NUWTUBE115
	3/0	GS-583/0P	US150	NUWTUBE150
	4/0	GS-584/0P	US150	NUWTUBE150
3/4"	#2 Sol	GS-342SR	US65	NUWTUBE65
	#2	GS-342R	US65	NUWTUBE65
	1/0	GS-341/0P	US115	NUWTUBE115
	2/0	GS-342/0P	US115	NUWTUBE115
	3/0	GS-343/0P	US150	NUWTUBE150
	4/0	GS-344/0P	US150	NUWTUBE150

*Copper-Clad ground rod nominal dimensions.

Cable to Steel Surface/Pipe Connections



c  US Listed 467


(Horizontal Cable to Horizontal Flat Steel Surface, ON Surface)

HD Connection Type

Cable Size	Mold Part No.	Weld Metal	
		UltraShot	NUWTUBE
#2 Sol	HD-2SA	US45	NUWTUBE45
#2	HD-2A	US45	NUWTUBE45
1/0	HD-1/0B	US90	NUWTUBE90
2/0	HD-2/0B	US90	NUWTUBE90
3/0	HD-3/0B	US115	NUWTUBE115
4/0	HD-4/0B	US115	NUWTUBE115
250 MCM	HD-25CMB	US115	NUWTUBE115

*For connections to pipe, please contact factory.

Cable to Steel Surface/Pipe Connections



c  US Listed 467

(Cable Down at 45° to Vertical Flat Steel Surface)

VA Connection Type

Cable Size	Mold Part No.	Weld Metal	
		UltraShot	NUWTUBE
#2 Sol	VA-2SB	US45	NUWTUBE45
#2	VA-2B	US45	NUWTUBE45
1/0	VA-1/0B	US90	NUWTUBE90
2/0	VA-2/0B	US90	NUWTUBE90
3/0	VA-3/0B	US115	NUWTUBE115
4/0	VA-4/0B	US115	NUWTUBE115
250 MCM	VA-25CMB	US115	NUWTUBE115



c  US Listed 467

(Cable Down at 45° to Side of Vertical or Horizontal Steel Pipe)

VA (Pipe) Connection Type (Range Taking)

Cable Size	Nominal Pipe Size	Mold Part No.	Weld Metal	
			UltraShot	NUWTUBE
#2 Sol	1/2" to 1" Pipe	VA-2SV.5X1B	US45	NUWTUBE45
	1-1/2" to 4" Pipe	VA-2SV1.5X4B	US45	NUWTUBE45
	4" to 6" Pipe	VA-2SV4X6B	US45	NUWTUBE45
	6" to 10" Pipe	VA-2SV6X10B	US45	NUWTUBE45
#2	1-1/2" to 4" Pipe	VA-2V1.5X4B	US45	NUWTUBE45
	4" to 6" Pipe	VA-2V4X6B	US45	NUWTUBE45
	6" to 10" Pipe	VA-2V6X10B	US45	NUWTUBE45
1/0	2" to 4" Pipe	VA-1/0V2X4B	US90	NUWTUBE90
	4" to 6" Pipe	VA-1/0V4X6B	US90	NUWTUBE90
	6" to 10" Pipe	VA-1/0V6X10B	US90	NUWTUBE90
2/0	2" to 4" Pipe	VA-2/0V2X4B	US90	NUWTUBE90
	4" to 6" Pipe	VA-2/0V4X6B	US90	NUWTUBE90
	6" to 10" Pipe	VA-2/0V6X10B	US90	NUWTUBE90
4/0	2" to 4" Pipe	VA-4/0V2X4B	US115	NUWTUBE115
	4" to 6" Pipe	VA-4/0V4X6B	US115	NUWTUBE115
	6" to 10" Pipe	VA-4/0V6X10B	US115	NUWTUBE115

Cable to Bus Bar Connections




c US Listed 467

(Horizontal Cable Tap to Edge of Horizontal Flat Busbar)

BE Connection Type

Bus/Lug Size	Cable Size	Mold Part No.	Weld Metal	
			UltraShot	NUWTUBE
1/4 x 1-1/2 & Wider	#6	BE-141.56B	US65	NUWTUBE65
	#2 Sol	BE-141.52SB	US65	NUWTUBE65
	#2	BE-141.52B	US65	NUWTUBE65
	1/0	BE-141.51/0B	US90	NUWTUBE90
	2/0	BE-141.52/0B	US90	NUWTUBE90
	3/0	BE-141.53/0B	US90	NUWTUBE90
3/8 x 1-1/2 & Wider	4/0	BE-141.54/0B	US90	NUWTUBE90
	1/0	BE-381.51/0B	US90	NUWTUBE90
	2/0	BE-381.52/0B	US90	NUWTUBE90
	3/0	BE-381.53/0B	US115	NUWTUBE115
1/2 x 1-1/2 & Wider	4/0	BE-381.54/0B	US115	NUWTUBE115
	1/0	BE-121.51/0B	US115	NUWTUBE115
	2/0	BE-121.52/0B	US115	NUWTUBE115
	3/0	BE-121.53/0B	US150	NUWTUBE150
	4/0	BE-121.54/0B	US150	NUWTUBE150

Cable to Reinforcing Steel Connections



c US Listed 467

Parallel Cable Tap of Horizontal Cable to Thru Horizontal Reinforcing Steel)


RP Connection Type

Size	Cable Size	Mold Part No.	Packing Mat'l No.	Weld Metal	
				UltraShot	Ultraweld
3	#6	RP-36B	WRPSLV	US25	NUWTUBE25
	#2	RP-32B	WRPSLV	US45	NUWTUBE45
	2/0	RP-32/0B	WRPSLV	US90	NUWTUBE90
	4/0	RP-34/0B	WRPSLV	US115	NUWTUBE115
4 & Larger	#6	RP-4L6A	CERPM1	US25	NUWTUBE25
	#2	RP-4L2A	CERPM1	US45	NUWTUBE45
4	2/0	RP-42/0B	WRPSLV	US90	NUWTUBE90
	4/0	RP-44/0B	WRPSLV	US115	NUWTUBE115
5	2/0	RP-52/0B	WRPSLV	US90	NUWTUBE90
	4/0	RP-54/0B	WRPSLV	US115	NUWTUBE115
6* & Larger	2/0	RP-6L2/0B	CERPM2	US90	NUWTUBE90
	4/0	RP-6L4/0B	CERPM2	US115	NUWTUBE115

*Requires #UMHDKIT Hold Down Kit for welds made to #6 and Larger reinforcing steel.

- (2) #WRPSLV Wrap Sleeves required per weld.
- (1) #CERPM1 or #CERPM2 Ceramic Packing Material required per weld.

Cable to Reinforcing Steel Connections



c US Listed 467

(Tee of Vertical Thru Reinforcing Steel & Horizontal Tap Cable)


7 & Larger

RE Connection Type

Size	Cable Size	Mold Part No.	Packing Mat'l No.	Weld Metal	
				UltraShot	NUWTUBE
3	#2	RE-32B	WRPSLV	US65	NUWTUBE65
	1/0	RE-31/0B	WRPSLV	US115	NUWTUBE115
	2/0	RE-32/0B	WRPSLV	US115	NUWTUBE115
	4/0	RE-34/0B	WRPSLV	US150	NUWTUBE150
4	#2	RE-42B	WRPSLV	US65	NUWTUBE65
	1/0	RE-41/0B	WRPSLV	US115	NUWTUBE115
	2/0	RE-42/0B	WRPSLV	US115	NUWTUBE115
	4/0	RE-44/0B	WRPSLV	US150	NUWTUBE150
5	#2	RE-52B	WRPSLV	US65	NUWTUBE65
	1/0	RE-51/0B	WRPSLV	US115	NUWTUBE115
	2/0	RE-52/0B	WRPSLV	US115	NUWTUBE115
	4/0	RE-54/0B	WRPSLV	US150	NUWTUBE150
6	#2	RE-62B	WRPSLV	US65	NUWTUBE65
	1/0	RE-61/0B	WRPSLV	US115	NUWTUBE115
	2/0	RE-62/0B	WRPSLV	US115	NUWTUBE115
	4/0	RE-64/0B	WRPSLV	US150	NUWTUBE150
7* & Larger	#2	RE-7L2K	CERPM3	US65	NUWTUBE65
	1/0	RE-7L1/0K	CERPM3	US115	NUWTUBE115
	2/0	RE-7L2/0K	CERPM3	US115	NUWTUBE115
	4/0	RE-7L4/0K	CERPM3	US150	NUWTUBE150

*Requires #CSKIT Chain Support Kit for welds made to #7 and Larger reinforcing steel.

- (1) #WRPSLV Wrap Sleeve required per weld.
- (1) #CERPM1 or #CERPM2 Ceramic Packing Material required per weld.



c US Listed 467

(Cross of Horizontal Cable Lapped Over Horizontal Reinforcing Steel)


RO Connection Type

Size	Cable Size	Mold Part No.	Packing Mat'l No.	Weld Metal	
				UltraShot	NUWTUBE
3	#6	RO-36B	WRPSLV	US65	NUWTUBE65
	#2	RO-32B	WRPSLV	US90	NUWTUBE90
	2/0	RO-32/0Q	WRPSLV	US115	NUWTUBE115
	4/0	RO-34/0Q	WRPSLV	US150	NUWTUBE150
4	#6	RO-46B	WRPSLV	US65	NUWTUBE65
	#2	RO-42B	WRPSLV	US90	NUWTUBE90
	2/0	RO-42/0Q	WRPSLV	US115	NUWTUBE115
	4/0	RO-44/0Q	WRPSLV	US150	NUWTUBE150
5	#6	RO-56B	WRPSLV	US65	NUWTUBE65
	#2	RO-52B	WRPSLV	US90	NUWTUBE90
	2/0	RO-52/0Q	WRPSLV	US115	NUWTUBE115
	4/0	RO-54/0Q	WRPSLV	US150	NUWTUBE150
6* & Larger	#6	RO-6L6B	CERPM1	US65	NUWTUBE65
	#2	RO-6L2B	CERPM1	US90	NUWTUBE90
	2/0	RO-6L2/0B	CERPM2	US115	NUWTUBE115
	4/0	RO-6L4/0B	CERPM2	US150	NUWTUBE150

*Requires #UMHDKIT Hold Down Kit for welds made to #6 and Larger reinforcing steel.

- (2) #WRPSLV Wrap Sleeves required per weld.
- (1) #CERPM1 or #CERPM2 Ceramic Packing Material required per weld.

Part No. - DRONE
(Pat. # US 9,562,751)



UltraShot® Features

- Patented copper drop-in cartridge consumed during the reaction process.
- The electronic ignition system fires instantly and uses a Milwaukee® M18™ REDLITHIUM™ 18 volt battery with a built in fuel gauge.
- Now with Audible Ignition Alert.
- Six-foot controller cord allows for flexibility in tight spaces as well as maintaining a safe distance from the reaction.

UltraShot® Benefits

- Cartridge is consumed leaving less waste such as plastic or metal containers on the job site.
- Long lasting **Ultra**-reliable ignition process allows for little to no downtime on the job site.
- UltraShot can be easily converted to the Low Smoke-No Flame system.

UltraShot® (Drop-In) Weld Metal

Size	Qty. Per Carton	Size	Qty. Per Carton
US25	20	US200	10
US32	20	US250	10
US45	20	US300	10
US65	20	US400	5
US90	10	US500	5
US115	10	US600	5
US150	10	US750	5



NUWTube®

- Uses the traditional method of ignition with starting powder.
- Innovative dual chamber design keeps weld metal and starting powder separate until point of use.
- Reduces material and labor costs by eliminating migrating starting powder issues.
- Less starting powder is needed, thereby reducing the amount of flash during the ignition process.

NUWTube® (Powder) Weld Metal

Size	Qty. Per Carton	Size	Qty. Per Carton
NUWTUBE15	20	NUWTUBE90	10
NUWTUBE25	20	NUWTUBE115	10
NUWTUBE32	20	NUWTUBE150	10
NUWTUBE45	20	NUWTUBE200	10
NUWTUBE65	20	NUWTUBE250	10

UltraShot® Low Smoke-No Flame System

Harger Lightning & Grounding offers the industry's best Low Smoke-No Flame System for indoor applications, confined spaces, high-risk fire environments and added safety for operators. The process uses standard Ultraweld molds, standard UltraShot weld metal and standard DRONE ignition system with a consumable filter to produce a finished connection with minimal smoke emission.

- The filter should be changed every connection to ensure the best performance.
- Ignition is accomplished with the use of the DRONE ignition system.

Kit Part No.	Fits Mold Price Key	Weld Metal Size	Filter Part No.	Filter Housing Part No.
USSKIT1	B, E, K, P, Q	25 thru 115	USSXFLR1.8	SAFHB25115
USSKIT2	B, E, K, P, Q	150 thru 300	USSXFLR2	SAFHB150300
USSKIT3	C, D, F, G, Y, Z	150 thru 500	USSXFLR3	SAFHC400


Kit Includes:

- (1) Adapter Clamp (USSXADPTR)
- (1) Filter Housing
- (10) Filters

- Filters sold as 10 pack.



Tools & Accessories



#MH1, #MH2
Mold Handle



#MSKIT
Magnetic Support Kit



#MLDSTBLZR
Mold Stabilizer Kit



#DRONE
Compact UltraShot
Controller
(Pat. # US 9,562,751)



#MIL1820BAT
Drone Battery



#MH6, #MH7
Mold Handle



#UMHDKIT
Hold Down Kit



#MCBRSH1
Mold Cleaning Brush
(large)



#USBOXKIT
Toolbox with UltraShot Trays
(UltraShot Sold Separately)



#MIL1812CHARGER
Drone Battery
Charger



#CSKIT
Chain Support Kit



#CCBRSH2
Cable Cleaning Brush



#CCBRSH1
Cable Cleaning Brush



#DRONECASE
Drone Controller
Storage Case

Uni-Shots



Listed



G11



G21



G31



G41

Type	NUWTUBE Mold Part No.	UltraShot Mold Part No.	Ground Rod Size	Cable Size Solid	Stranded
G11	G11-588NU	G11-588US	5/8"	#6, #8	#8
G11	G11-584NU	G11-584US	5/8"	#3, #4	#4, #6
G11	G11-582NU	G11-582US	5/8"	#1, #2	#2, #3
G21	G21-588NU	G21-588US	5/8"	#6, #8	#8
G21	G21-584NU	G21-584US	5/8"	#3, #4	#4, #6
G21	G21-582NU	G21-582US	5/8"	#1, #2	#2, #3
G31	G31-588NU	G31-588US	5/8"	#6, #8	#8
G31	G31-584NU	G31-584US	5/8"	#3, #4	#4, #6
G31	G31-582NU	G31-582US	5/8"	#1, #2	#2, #3
G41	G41-588NU	G41-588US	5/8"	#6, #8	#8
G41	G41-584NU	G41-584US	5/8"	#3, #4	#4, #6
G41	G41-582NU	G41-582US	5/8"	#1, #2	#2, #3
G11	G11-348NU	G11-348US	3/4"	#6, #8	#8
G11	G11-344NU	G11-344US	3/4"	#3, #4	#4, #6
G11	G11-342NU	G11-342US	3/4"	#1, #2	#2, #3
G21	G21-348NU	G21-348US	3/4"	#6, #8	#8
G21	G21-344NU	G21-344US	3/4"	#3, #4	#4, #6
G21	G21-342NU	G21-342US	3/4"	#1, #2	#2, #3
G31	G31-348NU	G31-348US	3/4"	#6, #8	#8
G31	G31-344NU	G31-344US	3/4"	#3, #4	#4, #6
G31	G31-342NU	G31-342US	3/4"	#1, #2	#2, #3
G41	G41-348NU	G41-348US	3/4"	#6, #8	#8
G41	G41-344NU	G41-344US	3/4"	#3, #4	#4, #6
G41	G41-342NU	G41-342US	3/4"	#1, #2	#2, #3

NOTE: For Full Size ground rod, add "F" after the ground rod size. Example: G3134F2US



Harger Lightning & Grounding

301 Ziegler Drive • Grayslake, IL 60030
Phone: 800-842-7437 • 847-548-8700
www.harger.com • hargersales@harger.com



UWLC-6.17