

One Hole, Standard Barrel, Compression Lugs

Part No.	Conductor Size (AWG)	Hardware Size	Color Code	Box Qty.	Approx. Box Wt. (lbs.)
GECL6	6	1/4"	Blue	50	1
GECL63/8	6	3/8"	Blue	50	2
GECL4	4	1/4"	Gray	50	1-1/2
GECL43/8	4	3/8"	Gray	50	2
GECL21/4	2	1/4"	Brown	50	2
GECL2	2	5/16"	Brown	50	2
GECL23/8	2	3/8"	Brown	50	2
GECL1/0	1/0	3/8"	Pink	10	1/2
GECL2/0	2/0	3/8"	Black	10	1
GECL4/0	4/0	1/2"	Purple	10	1
GECL250	250	1/2"	Yellow	10	2
GECL500	500	1/2"	Brown	5	2



cUL[®] US Listed 467
Listed 486



One Hole, Long Barrel, Compression Lugs

Part No.	Conductor Size (AWG)	Hardware Size	Inspection Port	Color Code	Box Qty.	Approx. Box Wt. (lbs.)
GECLB8NP	8	1/4"	No	Red	50	1
GECLB83/8NP	8	3/8"	No	Red	50	1
GECLB6	6	1/4"	Yes	Blue	50	1-1/2
GECLB63/8	6	3/8"	Yes	Blue	50	1-1/2
GECLB6NP	6	1/4"	No	Blue	50	1
GECLB63/8NP	6	3/8"	No	Blue	50	1
GECLB4	4	1/4"	Yes	Gray	50	2
GECLB43/8	4	3/8"	Yes	Gray	50	2
GECLB21/4	2	1/4"	Yes	Brown	50	2
GECLB21/4NP	2	1/4"	No	Brown	50	2
GECLB2	2	5/16"	Yes	Brown	50	2
GECLB23/8	2	3/8"	Yes	Brown	50	2
GECLB23/8NP	2	3/8"	No	Brown	50	2
GECLB1/0	1/0	3/8"	Yes	Pink	10	1
GECLB2/0	2/0	3/8"	Yes	Black	10	1
GECLB4/0	4/0	1/2"	Yes	Purple	10	2
GECLB250	250	1/2"	Yes	Yellow	10	2
GECLB500	500	1/2"	Yes	Brown	5	3



Has Inspection Port

cUL[®] US Listed 467
Listed 486



No Inspection Port

Two Hole, Long Barrel, Compression Lugs



UL Listed 467
US Listed 486



Part No.	Conductor Size (AWG)	O.C. Dim. B/T Holes	Hardware Size	Inspection Port	Color Code	Box Qty.	Approx. Box Wt. (lbs.)
GECLB82ANP	8	.625"	1/4"	No	Red	50	1-1/2
GECLB82CNP	8	1"	3/8"	No	Red	50	1-1/2
GECLB62A	6	.625"	1/4"	Yes	Blue	50	1-1/2
GECLB62ANP	6	.625"	1/4"	No	Blue	50	1-1/2
GECLB62B	6	.75"	3/8"	Yes	Blue	50	2
GECLB62C	6	1"	3/8"	Yes	Blue	50	2
GECLB62CNP	6	1"	3/8"	No	Blue	50	2
GECLB42A	4	.625"	1/4"	Yes	Gray	25	1-1/2
GECLB42B	4	.75"	1/4"	Yes	Gray	25	1-1/2
GECLB42C	4	1"	3/8"	Yes	Gray	25	2
GECLB22BS	2 Sol.	.75"	3/8"	Yes	White	25	2
GECLB22CS	2 Sol.	1"	3/8"	Yes	White	25	2-1/2
GECLB22CSNP	2 Sol.	1"	3/8"	No	White	25	2-1/2
GECLB22A	2	.625"	1/4"	Yes	Brown	25	1-1/2
GECLB22B	2	.75"	3/8"	Yes	Brown	25	1-1/2
GECLB22C	2	1"	3/8"	Yes	Brown	25	2
GECLB22CNP	2	1"	3/8"	No	Brown	25	2
GECLB1/02C	1/0	1"	3/8"	Yes	Pink	10	2
GECLB1/02D	1/0	1.75"	1/2"	Yes	Pink	10	2
GECLB2/02C	2/0	1"	3/8"	Yes	Black	10	1-1/2
GECLB2/02D	2/0	1.75"	1/2"	Yes	Black	10	1-1/2
GECLB3/02C	3/0	1"	3/8"	Yes	Orange	10	2
GECLB4/02C	4/0	1"	3/8"	Yes	Purple	10	2
GECLB4/02D	4/0	1.75"	1/2"	Yes	Purple	10	2-1/2
GECLB2502C	250	1"	3/8"	Yes	Yellow	10	3
GECLB2502D	250	1.75"	1/2"	Yes	Yellow	10	4
GECLB5002C	500	1"	3/8"	Yes	Brown	10	5
GECLB5002D	500	1.75"	1/2"	Yes	Brown	10	8
GECLB7502C	750	1"	3/8"	Yes	Black	10	10
GECLB7502D	750	1.75"	1/2"	Yes	Black	10	11

- Manufactured from electro tin plated copper.
- For use with copper or tinned copper conductors.

Two Hole, Slotted, Long Barrel, Compression Lugs



Part No.	Conductor Size (AWG)	Hole Spacing Range	Hardware Size	Inspection Port	Color Codes	Box Qty.	Approx. Box Wt. (lbs.)
GECLB62BC	6	.75" to 1"	3/8"	Yes	Blue	50	2
GECLB62BC250BK	6	.75" to 1"	3/8"	Yes	Blue	250	10
GECLB62BCNP	6	.75" to 1"	3/8"	No	Blue	50	2
GECLB62BCNP250BK	6	.75" to 1"	3/8"	No	Blue	250	10
GECLB22BCS	2 Sol.	.75" to 1"	3/8"	Yes	White	50	2
GECLB22BCS250BK	2 Sol.	.75" to 1"	3/8"	Yes	White	250	15
GECLB22BCSNP	2 Sol.	.75" to 1"	3/8"	No	White	25	2
GECLB22BCSN-P250BK	2 Sol.	.75" to 1"	3/8"	No	White	250	14
GECLB22BC	2	.75" to 1"	3/8"	Yes	Brown	50	3
GECLB22BC250BK	2	.75" to 1"	3/8"	Yes	Brown	250	15
GECLB22BCNP	2	.75" to 1"	3/8"	No	Brown	25	2
GECLB22BCNP250BK	2	.75" to 1"	3/8"	No	Brown	250	16

- Manufactured from electro tin plated copper.
- For use with copper or tinned copper conductors.
- 250 pack comes in one gallon bucket.

Long Barrel Butt Splices

Part No.	Conductor Size (AWG)	Box Qty.	Approx. Box Wt. (lbs.)
CLBBS8	8	50	1
CLBBS6	6	50	1
CLBBS4	4	50	2
CLBB2S	2 Sol.	50	4
CLBBS2	2	50	4
CLBBS2/0	2/0	10	2
CLBBS4/0	4/0	10	2
CLBBS250	250	10	3
CLBBS500	500	10	5



Specialized Compression Lugs



GECLB62EIA

UL Listed 467
US Listed 486



GECLB62EIA90

Part No.	Conductor Size (AWG)	Hole Spacing Range	Hardware Size	Bend Angle	Color Code	Box Qty.	Approx. Box Wt. (lbs.)
GECLB62EIA	6 or 6 FLEX	.5" - .625"	1/4"	No Bend	Blue	50	1-1/2
GECLB62EIA90	6 or 6 FLEX	.5" - .625"	1/4"	90°	Blue	50	1-1/2

- Designed to fit standard EIA spacing.

NOTES:

- Manufactured from electro tin plated copper.
- For use with copper or tinned copper conductors.
- Lugs have inspection ports.

C-Type Compression Taps

Heavy Duty C-Taps

Part No.	Conductor (AWG)		Die Index	Box Qty.	Approx. Box Wt. (lbs.)
	Run	Tap			
CT4666	#4 Stranded #6 Solid	#6 Stranded #6 Solid	BG	50	2-1/2
CT4446	#4 Stranded #6 Solid	#4 Stranded #4 Solid	BG	50	2-1/2
CT2248	#2 Stranded #2 Solid	#4 Stranded #8 Solid	C	50	6
CT2222	#2 Stranded #2 Solid	#2 Stranded #2 Solid	C	50	4
CT22/0	2/0 Stranded 1/0 Solid	#2 Stranded #8 Solid	O	10	1
CT24/0	4/0 Stranded 3/0 Solid	#2 Stranded #6 Solid	D3	10	1
CT2/02/0	2/0 Stranded 1/0 Solid	2/0 Stranded 1/0 Solid	O	10	1
CT4/02/0	4/0 Stranded 3/0 Solid	2/0 Stranded 1/0 Solid	D3	10	2
CT4/04/0	4/0 Stranded 3/0 Solid	4/0 Stranded 3/0 Solid	D3	10	2



UL Listed 467
US Listed 486

Antioxidant Joint Compound

Aluminum

Part No.	Size	Box Qty.	Approx. Box Wt. (lbs.)
HAAJC1/2	1/2 oz.	12	1/2
HAAJC8	8 oz.	12	6

- Oxide inhibiting joint compound used to improve electrical conductivity and enhance the integrity of the connection.
- Synthetic base with suspended zinc particles.
- Material is gray in color.
- Recommended for aluminum to aluminum connections, aluminum to copper connections and aluminum conduit threads.



Copper

Part No.	Size	Box Qty.	Approx. Box Wt. (lbs.)
HCAJC1/2	1/2 oz.	12	1/2
HCAJC8	8 oz.	12	6

- Oxide inhibiting joint compound used to improve electrical conductivity and enhance the integrity of the connection.
- Synthetic base with suspended copper particles.
- Material is copper in color.
- Recommended for copper to copper connections, copper threads and all grounding applications.



Part No.	Qty.	Unit Wt. (oz.)
NOOXCLR	EA	8

NO•OX•ID® Antioxidant Paste

Cold applied clear antioxidant for aluminum to aluminum, aluminum to copper and copper to copper connections.



Mechanical Compression Tools



Part No.	Length	Approx. Each Wt. (lbs.)
MCT	24"	5

- Dieless adjustable compression tool with steel handle.
- Works with copper conductor sizes #8 AWG through 250 MCM and aluminum conductors #8 AWG through 4/0.
- For use with compression lugs and light duty compression taps.
- Approximately 2 tons of force.



Part No.	Length	Approx. Each Wt. (lbs.)
MCT101/0	10-1/2"	3

- Works with copper compression lugs sizes #10 through 1/0.
- Handle length facilitates two-handed crimps when necessary.
- Approximately 2 tons of force.
- Dies included.

Other Harger Products / Services

Grounding Busbars



Fence Grounding



Wireless Communication Equipment



Grounding Connectors



Ultraweld® Exothermic Connections
featuring UltraShot® & NUWTube®



Supplementary Bonding Grids
aka Signal Reference Grids



Specialized Ground Electrodes



Data-Com Bonding & Grounding



Lightning Protection Installation Training



Harger Lightning & Grounding
301 Ziegler Drive • Grayslake, IL 60030
Phone: 800.842.7437 • Fax: 847.548.8755
Website: www.harger.com • Email: hargersales@harger.com



CCLC-2.20